



A  $\varnothing$  120 for lines (does not apply to machines with MCU30)  
 B  $\varnothing$  120 for container discharge (optional, not for machines with MCU30)

The Melitta® Cafina® XT7 is delivered ready for connection. However, before setting it up, the connections required on site must have been installed within a radius of 1 m so that they are easily accessible. This preliminary work must be carried out by authorized specialists in compliance with the applicable regulations. Melitta® Customer Service is not authorized to carry out this work and does not assume any responsibility for the installation.

The machine must be positioned on a level table top. The supply lines must be routed from underneath. To insert the connection hoses and the connection cables, an aperture is to be provided in the table top underneath each unit measuring approx.  $\varnothing$  120 mm (A). For machines with container discharge (optional), an additional aperture of approx.  $\varnothing$  120 mm (B) is required.

With the feet installed, the units can be raised by approx. 15 mm.

**Unit specifications:**

Hourly output*:	approx. 25 l hot water approx. 150 cups of café crème	Dimensions (W x D x H):	300 x 580 x 715 mm
		Installation weight:	approx. 60 kg
Permissible ambient temperature:	5 °C - 30 °C	Coffee bean supply:	2 x 3 l / 2 x approx. 1000 g
Permissible air humidity:	< 80 % non-condensing	Instant container capacity:	1 x 1.7 l / 1 x approx. 1300 g or 2 x 1 l / 2 x approx. 450 - 800 g
		Grounds drawer capacity:	for approx. 30 portions

\* With 230 V.

Suction height of milk pump max. 700 mm from bottom edge of machine (tube length max. 1200 mm).

**Electrical connection (a):**

Mains connection:	200 - 240 V / 50 - 60 Hz – via 1.8 m power cable with Schuko mains plug
Power consumption:	2175 - 3040 W
On-site fuse:	16 A required

The connections must be established using easily accessible Schuko sockets. These must be protected with a residual current circuit breaker (max. 30 mA).

**Water connection (b):**

Fresh water connection: G 3/4" outer thread

A shut-off valve, which makes it possible to connect this machine in accordance with national regulations, such as EN 61770, must be installed in an easily accessible place. The machine is supplied with the corresponding connection hoses.

Fresh water pressure: min. 0.25 MPa (2.5 bar) at approx. 2 l/min  
 a pressure reducer is required for static pressures above 0.6 MPa (6 bar)

Fresh water carbonate hardness: 1 °dKH - 3 °dKH: no action required  
 4 °dKH and above: decarbonization system required (e.g., BRITA Purity)  
 less than 1 °dKH: consult Melitta®

Waste water connection: at least DN 25 - NW 1" – a ventilated odor trap is to be provided

The Melitta® Cafina® XT7 is fitted with two nozzles for the drain of waste water. These must be connected to a water drain on site using the hoses supplied.

[www.planerhandbuch.de](http://www.planerhandbuch.de)

Date: 12/2018  
 Page: 1/1

Subject to changes.  
 Property of Melitta®.  
 Reproduction prohibited.



**Melitta® Cafina® XT7**  
**(200 - 240 V)**  
 Dimension and datasheet

All dimensions are approximate dimensions in millimeters.